

## Chapter NR 666

### APPENDIX II

#### TIER I AND TIER II FEED RATE SCREENING LIMITS FOR TOTAL CHLORINE

| Terrain-adjusted effective<br>stack height (m) | Noncomplex Terrain |              | Complex Terrain |
|------------------------------------------------|--------------------|--------------|-----------------|
|                                                | Urban (g/hr)       | Rural (g/hr) | (g/hr)          |
| 4                                              | 8.2E+01            | 4.2E+01      | 1.9E+01         |
| 6                                              | 9.1E+01            | 4.8E+01      | 2.8E+01         |
| 8                                              | 1.0E+02            | 5.3E+01      | 4.1E+01         |
| 10                                             | 1.2E+02            | 6.2E+01      | 5.8E+01         |
| 12                                             | 1.3E+02            | 7.7E+01      | 7.2E+01         |
| 14                                             | 1.5E+02            | 9.1E+01      | 9.1E+01         |
| 16                                             | 1.7E+02            | 1.2E+02      | 1.1E+02         |
| 18                                             | 1.9E+02            | 1.4E+02      | 1.2E+02         |
| 20                                             | 2.1E+02            | 1.8E+02      | 1.3E+02         |
| 22                                             | 2.4E+02            | 2.3E+02      | 1.4E+02         |
| 24                                             | 2.7E+02            | 2.9E+02      | 1.6E+02         |
| 26                                             | 3.1E+02            | 3.7E+02      | 1.7E+02         |
| 28                                             | 3.5E+02            | 4.7E+02      | 1.9E+02         |
| 30                                             | 3.9E+02            | 5.8E+02      | 2.1E+02         |
| 35                                             | 5.3E+02            | 9.6E+02      | 2.6E+02         |
| 40                                             | 6.2E+02            | 1.4E+03      | 3.3E+02         |
| 45                                             | 8.2E+02            | 2.0E+03      | 4.0E+02         |
| 50                                             | 1.1E+03            | 2.6E+03      | 4.8E+02         |
| 55                                             | 1.3E+03            | 3.5E+03      | 6.2E+02         |
| 60                                             | 1.6E+03            | 4.6E+03      | 7.7E+02         |
| 65                                             | 2.0E+03            | 6.2E+03      | 9.1E+02         |
| 70                                             | 2.3E+03            | 7.2E+03      | 1.1E+03         |
| 75                                             | 2.5E+03            | 8.6E+03      | 1.2E+03         |
| 80                                             | 2.9E+03            | 1.0E+04      | 1.3E+03         |
| 85                                             | 3.3E+03            | 1.2E+04      | 1.4E+03         |
| 90                                             | 3.7E+03            | 1.4E+04      | 1.6E+03         |
| 95                                             | 4.2E+03            | 1.7E+04      | 1.8E+03         |
| 100                                            | 4.8E+03            | 2.1E+04      | 2.0E+03         |
| 105                                            | 5.3E+03            | 2.4E+04      | 2.3E+03         |
| 110                                            | 6.2E+03            | 2.9E+04      | 2.5E+03         |
| 115                                            | 7.2E+03            | 3.5E+04      | 2.8E+03         |
| 120                                            | 8.2E+03            | 4.1E+04      | 3.2E+03         |